



THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION  
 © COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
GP	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
		E		PER ECR-06-020659	04SEP06	WW	WW

Tooling Drawing NO.  
 USB A: TR00662  
 USB B: TR00664



PIN ASSIGNMENT :



TYCO P/N  
 T/D YYWW  
 MADE IN CHINA

LABEL

PART NO.	1487594-1	1487594-2	1487594-3	1487594-4	1487594-5
LENGTH(L)	500	250	162	310	750

- NOTES:
- TESTED FOR CONTINUITY, SHORTS AND OPENS, HI-POT 630V FOR 10MS.
  - CABLE ASSEMBLY MEETS USB 2.0 STANDARDS.
  - EXPOSED CABLE BRAID IS NOT PERMISSIBLE BEYOND OVERMOLD.
  - THE FINAL CABLE ASSEMBLY MAXIMUM LENGTH NOT TO EXCEED 1000MM PER USB SPECIFICATIONS.
  - MEETS REQUIREMENTS OF EU DIRECTIVE 2002/95/EC

AR	AR	AR	AR	AR	MR	COPPER FOIL, W: 5MM	6
1	1	1	1	1	PC	LABEL 25*35MM, WHITE: 25*13	5
AR	AR	AR	AR	AR	KG	Overmold PVC, 40P, Color: Black(BK01)	4
AR	AR	AR	AR	AR	M1	USB 2.0 Cable 28AWG*1P+28AWG*2C+Al/Mylar +Drain+Braid, Color: Black(BK01), OD: 4.20±0.15mm	3
1	1	1	1	1	PC	USB 4Pin Connector Contacts: Gold 30U Plated, Shell: Nickel Plated, Housing UL94V-0 B Type.	2
1	1	1	1	1	PC	USB 4Pin Connector Contacts: Gold 30U Plated, Shell: Nickel Plated, Housing UL94V-0 A Type.	1
-5	-4	-3	-2	-1	U/M	DESCRIPTION	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	BOVEY LIU	25FEB02	Tyco Electronics Corporation Harrisburg, Pa 17105-3608			
DIMENSIONS: mm		CHK	J.HUNT	25FEB02				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	J.HUNT	25FEB02	NAME			
0 PLC ± -		PRODUCT SPEC		CABLE ASSEMBLY, USB A TYPE TO USB B TYPE				
1 PLC ± -		APPLICATION SPEC		-				
2 PLC ± -		-		-				
3 PLC ± -		-		-				
4 PLC ± -		-		SIZE		CAGE CODE	DRAWING NO	RESTRICTED TO
ANGLES ± -		-		A3		00779	C-1487594	-
FINISH		-		WEIGHT		-		SCALE
-		-		-		-		SHEET 1 OF 1
-		-		-		-		REV E

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1487594-1](#)