


Deep groove ball bearings, single row, unsealed



Principal dimensions			Basic load ratings		Fatigue load limit P_u	Speed ratings		Mass	Designation
d	D	B	dynamic	static		Reference speed	Limiting speed		
mm			kN		kN	r/min		kg	-
25	62	17	23,4	11,6	0,49	24000	16000	0,23	6305 *



Calculation factors

k_r 0,03
 f_0 12