

Han 16B HBM Rear-Fit DL w/o frame



Part number	09 30 016 0392
Specification	Han 16B HBM Rear-Fit DL w/o frame
HARTING eCatalogue	https://b2b.harting.com/09300160392

Identification

Category	Hoods/Housings
Series of hoods/housings	Han® B
Type of hood/housing	Bulkhead mounted housing
Description of hood/housing	Rear mounting
Type	Low construction

Version

Locking type	Double locking lever
Han-Easy Lock®	Yes
Size	16 B
Field of application	Standard hoods/housings for industrial connectors

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4 4X 12

Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)
Material (seal)	NBR
Material (locking)	Polycarbonate



Pushing Performance

Material properties

	Stainless steel
Colour (locking)	RAL 7037 (dust grey)
Material flammability class acc. to UL 94 (locking levers)	V-0

Specifications and approvals

Approvals	DNV GL
-----------	--------

Commercial data

Packaging size	1
Country of origin	China
European customs tariff number	85389099
eCl@ss	27440202 Shell for industrial connectors