



Label printer | thermal | max. 104 mm

Product code: 50243

The thermal printer quickly and efficiently produces prints on special thermal paper without the need for toner or ink.

TECHNICAL DATA

PRINTING METHOD	Thermal
RESOLUTION	203 dpi
PRINTING WIDTH	104 mm
PAPER WIDTH	26.7 mm - 104 mm
PRINTING SPEED	127 mm/s
MEMORY	RAM: 8MB, Flash: 4MB (expandable to 8MB)
DETECTING THE PAPER	Gap sensor, paper end sensor, uncover sensor, black mark sensor
INTERFACE	USB, Ethernet, Serial
DRIVERS SUPPORT	XP/Win 7/Win 8/Win 10
PRINTING BARCODES	Code 39, Code 93, ITF, EAN 128, Code 128, subsets A, B, C, Codabar, EAN-8, EAN-13, UPC-A, UPC-E, EAN and UPC 2(5), digits, add-on, MSI, MSIC, PLESSEY, CPOST, ITF 14, EAN 14
PAPER TYPE	Labels, continuation paper, black mark paper
INPUT POWER SUPPLY	24V / 2.5A
PAPER THICKNESS	0.06 mm - 0.2 mm
PRINTING LIFE	50 km
USAGE	Cash registers Fiscal printers
WEIGHT	1.4 kg

DIMENSIONS

217 x 182 x 172 mm

STORAGE TEMPERATURES

-10 C to +60 C

HUMIDITY

10% - 90% (non-condensing)

EAN CODE

5901878502434