


















- Screw terminal
- Crimp terminal

Number of contacts

16 + 



Style	Ordering number		Description	Outline drawing dimensions in mm
	Male insert	Female insert		
Screw connection with wire protection  	43.12.16.40	43.22.16.40	HE.16.Sti.S	Contact arrangement view from termination side Sti  Bu 
		42.10.16.00	HE.16.Bu.S	
without wire protection  	42.10.16.00	42.20.16.00	HB.16.Sti.S	Series HE / HX Sti  * 19.5 M3x10 Bu 
		66.12.16.40	HB.16.Bu.S	
with wire protection  	66.12.16.40	66.22.16.40	HX.16.Sti.S	Series HB Sti  * 19.5 M3x10 Bu 
		43.12.16.41	HX.16.Bu.S	
Crimp terminal please order crimp contacts separately (refer to page)  	43.12.16.41	43.22.16.41	HE.16.Sti.C	*distance for guaranteed contact 21 mm max. Panel cut-out for contact insert when used without housing 
		43.12.16.41	HE.16.Bu.C	