


**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **0593708100**  
**Status:** **Active**  
**Description:** 2.00mm Pitch Crimp Terminal, Female, 22-28 AWG, Bag

**Documents:**

<a href="#">3D Model</a>	<a href="#">Product Specification PS-51216-007-001 (PDF)</a>
<a href="#">3D Model (PDF)</a>	<a href="#">Product Specification PS-51353-010-001 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Application Specification 5055960000-AS-000 (PDF)</a>
<a href="#">Product Specification 5055960000-PS-000 (PDF)</a>	<a href="#">Application Specification 5055960000-AS-001 (PDF)</a>
<a href="#">Product Specification 513820000-PS-001 (PDF)</a>	<a href="#">Packaging Specification SPK-59370-001-001 (PDF)</a>
<a href="#">Product Specification PS-51216-006-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>



**General**

Product Family	Crimp Terminals
Series	59370
Application	Signal, Wire-to-Board
Crimp Quality Equipment	Yes
Packaging Alternative	593708000 (Reel)
Product Name	MicroTPA, MUO 2.5
UPC	800754824330

**Physical**

Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	61.000/mg
Packaging Type	Bag
Plating min - Mating	0.889µm
Plating min - Termination	0.914µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	0.90-1.50mm
Wire Size AWG	22, 24, 26, 28
Wire Size mm <sup>2</sup>	N/A

**Electrical**

Voltage - Maximum	250V AC (RMS)/DC
-------------------	------------------

**Material Info**

**Reference - Drawing Numbers**

Application Specification	5055960000-AS-000, 5055960000-AS-001
Crimp Specification	593700000-CS-000
Packaging Specification	SPK-59370-001-001
Product Specification	5055960000-PS-000, 513820000-PS-001, PS-51216-006-001, PS-51216-007-001, PS-51353-010-001
Sales Drawing	SD-59370-004-001

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2020)4578-DC (25  
June 2020)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

59370 Series

**Use With**

Housings [51216](#) , [505596](#)

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

Description	Product #
-------------	-----------

Extraction and	<a href="#">638132700</a>
----------------	---------------------------

Activation Tool	
-----------------	--

Hand Crimp Tool	<a href="#">638192600</a>
-----------------	---------------------------

for 2.00mm Crimp

Terminals, 22-28

AWG

**Japan**

Description	Product #
-------------	-----------

Hand Crimp Tool	<a href="#">574045000</a>
-----------------	---------------------------

This document was generated on 08/10/2020

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**