

KEMET Part Number: ALC10S1104DL
(A526EP103M080S)

ALC10S, Aluminum Electrolytic, 10,000 uF, 20%, 80 VDC, -40/+85°C



General Information

Series:	ALC10S
Dielectric:	Aluminum Electrolytic
Description:	Audio Grade Snap-In
Features:	Audio Grade
RoHS:	Yes
Lead:	2 Pin
AEC-Q200:	No
Notes:	Dimensions Include Sleevings
Shelf Life:	156 Weeks

Dimensions

D	35mm NOM
L	80mm NOM
S	10mm +/-0.1mm
LL	6.3mm +/-1mm
F	2mm +/-0.1mm

Specifications

Capacitance:	10,000 uF
Capacitance Tolerance:	20%
Voltage DC:	80 VDC
Temperature Range:	-40/+85°C
Rated Temperature:	85°C
Life:	15000 Hrs
Leakage Current:	4800 uA (5min 20°C)

Packaging Specifications

Weight:	105 g
Sleevings:	Yes
Packaging:	Bulk, Bag

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[KEMET:](#)

[ALC10S1104DL](#)