


SPECIFICATIONS

Performance level	PL2
Filter type	C
Capacitance	3900 pF±20%
Working voltage	100 V
Current rating	7,5 A
Insulation resistance	>1 GΩ

FREQUENCY (MHz)	ATTENUATION (dB)
5	6
10	11
50	25
100	35
500	35
1000	32

PCB layout, component side, thickness 1,6 mm

			Dot.	Name	 All Dim. in mm Orig. Size DIN A 4	
			Detail.	08/07/02		CV
36283	12/01/12	SD	Insp.	12/01/12		JB
EC01003	25/11/09	PK	Stand.			
33790	02/08/06	PK				
31058	08/07/02	CV				
Mod.	Dot.	Name	HARTING EURL F-95972 Paris			

D-Sub, male, angled, 25 poles, turned solder pins, clinch nuts and brackets with board locks	Maßstab/ Scale
	1,5:1
TB 09 64 324 724X	Blatt/ Page
	1 / 4
Sub.	

09 64 324 7243	M3
09 64 324 7242	4-40 UNC-2B
Part number	Nut thread

D  
C  
B  
A

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09643247242](#)