

# Torque screwdriver TorqueVario®-S variably adjustable torque limit 0.4 - 1 (26461)



Tools that work for you

Wiha Werkzeuge GmbH  
Obertalstraße 3-7 78136 Schonach  
E-Mail: info.de@wiha.com  
Tel.: +49 (0)7722 959-0

Order no.: 26461

Article number: 28521100

EAN: 4010995264611

Customs tariff number: 82054000

Meets your requirements: Variably adjustable torque covers a wide range of applications.  
Increases your efficiency: The correct torque protects material from damage and means no follow-up work.

Protects your health: With the patented SoftFinish® handle design, ensuring work is kind to hands and muscles. Recommended by doctors and therapists at German Campaign for Healthier Backs.

Lowers your costs: The correct torque protects you from warranty claims.

Application: For applications where recommended torque settings are important. Use in combination with a Wiha torque interchangeable blade.

Extra: Incl. works inspection protocol.

Extra: Delivered in practical plastic box.

Precision:  $\pm 6\%$ , tracing to national standards (see table for other tolerances).

Handle: Torque infinitely adjustable with Torque-Setter setting tool (also supplied).

Handle: Ergonomic multi-component handle, particularly light and compact.

Handle: Handle sizes proportioned to optimise torque setting.

Handle: Audible and perceptible click when the pre-set torque has been attained.

Handle: Compatible with all blades of the 2859.

For applications in mechanics

Bit holders or blades are not included in delivery.

DIN EN ISO 6789.

---

Customs tariff number	82054000
-----------------------	----------

---

Tolerance	6 %
-----------	-----

---

Torque range min (Nm)	0.4 Nm
-----------------------	--------

---

Torque range max (Nm)	1 Nm
-----------------------	------

---

Blister packed	No
----------------	----

---

Handle diameter	23 mm
-----------------	-------

---

Hexagon head 1 (mm)	4.0 mm
---------------------	--------

---

Handle length	127 mm
---------------	--------

---

VDE article	No
-------------	----

---

Country of origin (ISO 3166-1 Alpha 3)	DEU
---	-----

---