




## **Datasheet**

# RS 2mm 20 Way 1 Row Straight PCB Socket Through Hole Socket Strip

**RS Stock number <u>605-8774</u>** 

Dimensions (mm)



## **Specifications**

## Material

Moulding: Nylon 6T 940V-0 Black

Contacts: Phosphor Bronze

Finish: Nickel

42 Gold on contact area /

100% tin on finish (matt) on tails

## Mechanical

Insertion Force – 2N max Withdrawal force – 0.2 min Durability – 1000 operations

#### **Electrical**

Current rating: 1A AC/C Voltage proof: 500V AC min

Contact resistance: 20 milliohms max Insulation resistance: 1000 megohms max Dielectric withstanding: 500V AC for 1min

**Environmental** 

Temperature range -40 °C to +105 °C



# **ENGLISH**

## **Specifications**

## **Material**

Moulding: Nylon 6T 940V-0 Black

Contacts: Phosphor Bronze

Finish: Nickel

42 Gold on contact area / 100% tin on finish (matt) on tails

## Mechanical

Insertion Force – 2N max Withdrawal force – 0.2 min Durability – 1000 operations

## **Electrical**

Current rating: 1A AC/C Voltage proof: 500V AC min

Contact resistance: 20 milliohms max Insulation resistance: 1000 megohms max Dielectric withstanding: 500V AC for 1min

## **Environmental**

Temperature range -40 °C to +105 °C