

Han 75DDD M-c



Image is for illustration purposes only. Please refer to product description.

Part number	09 16 075 2001
Specification	Han 75DDD M-c
HARTING eCatalogue	https://b2b.harting.com/09160752001

Identification

Category	Inserts
Series	Han [®] DDD

Version

Termination method	Crimp termination
Gender	Male
Size	10 B
Number of contacts	75
PE contact	Yes
Details	PE connection with a Han D [®] crimp contact Please order crimp contacts separately.

Technical characteristics

Conductor cross-section	0.14 ... 2.5 mm ²
Rated current	10 A
Rated voltage	250 V
Rated impulse voltage	4 kV
Pollution degree	3
Insulation resistance	>10 ¹⁰ Ω
Limiting temperature	-40 ... +125 °C
Mating cycles	≥500



Pushing Performance

Material properties

Material (insert)	Polycarbonate (PC)
Colour (insert)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0

Specifications and approvals

Specifications	IEC 61984
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076

Commercial data

Packaging size	1
Net weight	51.22 g
Country of origin	China
European customs tariff number	85366990
eCl@ss	27440205 Contact insert for industrial connectors

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09160752001](#)