



### Certifications & Ratings

- RoHS compliant
- NEMA 4X (Watertight only)
- IP66 (Watertight only)

### Application

The 607 Series LED Panel Mount Indicators are designed for a variety of applications such as:

- Main power indication
  - Remote power indication
  - Status indication
  - Maintenance and warning indication
  - Instrumentation
- ... and many more!

### Dimensions

inches [mm]




Figure 1




Figure 2




Figure 3




Figure 4

### Mechanical Information

- Mounting Hole Size:** 0.283" (7.2 mm)
- Max Panel Thickness:** See part numbers
- Mounting Torque:** 0.362 lbs/ft (5 kg/cm)  
0.217 lbs/ft or 3 kg/cm (Figure 5 only)

### Specifications

- Voltage Options:** 2 VDC (resistor required)  
6, 12 & 24 VDC (no resistor required)
- Operating Temp:** -30°C to +85°C (-22°F to +185°F)
- Storage Temp:** -40°C to +85°C (-40°F to +185°F)
- Electrical Connection:** Solder terminals
- Housing:** Protruding & recessed positions:  
Brass—Chrome Plated  
Internal position: Polycarbonate
- Terminals:** Copper—Nickel Plated
- Lock Washer:** Iron—Nickel Plated
- Nut:** Brass—Nickel Plated




Figure 5

## Ordering Information 607 Series

Standard		Watertight								
Part Number	Part Number	Color	Voltage (VDC)	Current (mA)	Intensity Typ. (mcd)	LED Positions	Figure	Panel Thickness		
607-1112-110F	607-1112-310F	● Red	2	15	40	Protruding	1	0.187" (4.75 mm)		
607-1212-110F	607-1212-310F	● Green			65					
607-1312-110F	607-1312-310F	● Yellow			55					
607-1112-120F	607-1112-320F	● Red	6		40		Recessed		2	0.265" (6.75 mm)
607-1212-120F	607-1212-320F	● Green			65					
607-1312-120F	607-1312-320F	● Yellow			55					
607-1112-130F	607-1112-330F	● Red	12		40	Internal		3	0.136" (3.45 mm)	
607-1212-130F	607-1212-330F	● Green			65					
607-1312-130F	607-1312-330F	● Yellow			55					
607-2112-110F	607-2112-310F	● Red	2		65		Recessed	4		0.336" (8.50 mm)
607-2212-110F	607-2212-310F	● Green			85					
607-2312-110F	607-2312-310F	● Yellow			70					
607-2112-120F	607-2112-320F	● Red	6		65	Internal		5	0.187" (4.75 mm)	
607-2212-120F	607-2212-320F	● Green			85					
607-2312-120F	607-2312-320F	● Yellow			70					
607-2112-130F	607-2112-330F	● Red	12	65	Internal		5	0.187" (4.75 mm)		
607-2212-130F	607-2212-330F	● Green		85						
607-2312-130F	607-2312-330F	● Yellow		70						
607-3132-120F	607-3132-320F	● Red	6	35		Internal	5		0.187" (4.75 mm)	
607-3232-120F	607-3232-320F	● Green		45						
607-3332-120F	607-3332-320F	● Yellow		40						
607-3132-130F	607-3132-330F	● Red	12	35	Internal		5	0.187" (4.75 mm)		
607-3232-130F	607-3232-330F	● Green		45						
607-3332-130F	607-3332-330F	● Yellow		40						
607-3132-140F	607-3132-340F	● Red	24	35		Internal	5		0.187" (4.75 mm)	
607-3232-140F	607-3232-340F	● Green		45						
607-3332-140F	607-3332-340F	● Yellow		40						

Dialight reserves the right to make changes at any time in order to supply the best product possible. The most current version of this document will always be available at: [www.dialightsignalsandcomponents.com](http://www.dialightsignalsandcomponents.com)  
**Warranty Statement:** Except for the warranty expressly provided for [herein/above/below], Dialight disclaims any and all other warranties, express or implied, including, without limitation, any warranties of merchantability, fitness for a particular purpose, title, and noninfringement.



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Dialight:

[607-1212-120F](#) [607-1112-120F](#) [607-2312-130F](#) [607-2112-110F](#) [607-2312-110F](#) [607-2312-120F](#) [607-2212-110F](#)  
[607-3232-120F](#) [607-2112-130F](#) [607-2212-120F](#) [607-2112-120F](#) [607-3232-130F](#) [607-2212-130F](#) [607-3132-120F](#)  
[607-1212-130F](#) [607-1112-130F](#) [607-1212-110F](#) [607-3132-130F](#) [607-3332-120F](#) [607-1312-120F](#) [607-3332-130F](#)  
[607-1312-110F](#) [607-1112-110F](#) [607-1312-130F](#) [607-3132-140F](#) [607-1312-310F](#) [607-3332-340F](#) [607-3132-340F](#)  
[607-3132-330F](#) [607-1212-320F](#) [607-3232-140F](#) [607-3232-340F](#) [607-2212-330F](#) [607-3332-330F](#) [607-1112-330F](#)  
[607-2312-310F](#) [607-1112-310F](#) [607-1212-310F](#) [607-2212-310F](#) [607-2112-330F](#) [607-1212-330F](#) [607-2112-310F](#)  
[607-3132-320F](#) [607-2312-330F](#) [607-3232-330F](#) [607-1112-320F](#) [607-1312-330F](#) [607-3332-140F](#) [607-2312-320F](#)  
[607-2412-120F](#) [607-2512-120F](#) [607-1115-320F](#) [607-1115-330F](#) [607-1215-320F](#) [607-1215-330F](#) [607-1315-320F](#)  
[607-1315-330F](#) [607-2115-320F](#) [607-2115-330F](#) [607-2215-320F](#) [607-2215-330F](#) [607-2315-320F](#) [607-2315-330F](#)  
[607-3135-320F](#) [607-3135-330F](#) [607-3135-340F](#) [607-3235-320F](#) [607-3235-330F](#) [607-3235-340F](#) [607-3335-320F](#)  
[607-3335-330F](#) [607-3335-340F](#) [607-1412-110F](#) [607-1412-120F](#) [607-1512-110F](#) [607-1512-120F](#) [607-2412-110F](#)  
[607-2412-130F](#) [607-2412-140F](#) [607-2415-120F](#) [607-2415-130F](#) [607-2415-140F](#) [607-2512-110F](#) [607-2512-130F](#)  
[607-2512-140F](#) [607-2515-120F](#) [607-2515-130F](#) [607-2515-140F](#)