

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0768290108](#)
Status: **Active**
Overview: [Mega-Fit Power Connectors](#)
Description: Mega-Fit Slim Vertical Header, Through Hole, 5.70mm Pitch, Dual Row, 8 Circuits, 1.52µm Tin (Sn) Plating, Glow-Wire Capable, Black

Documents:

3D Model	Application Specification AS-76823-100-001 (PDF)
3D Model (PDF)	Packaging Specification 768291100-000 (PDF)
Drawing (PDF)	Test Summary TS-76823-100-001 (PDF)
Product Specification PS-76823-100-001 (PDF)	RoHS Certificate of Compliance (PDF)
Application Specification 768232000-AS-000 (PDF)	Product Literature (PDF)


General

Product Family	PCB Headers
Series	76829
Application	Power, Wire-to-Board
Overview	Mega-Fit Power Connectors
Product Name	Mega-Fit
UPC	889056895576

Physical

Breakaway	No
Circuits (Loaded)	8
Circuits (maximum)	8
Color - Resin	Black
Durability (mating cycles max)	25
First Mate / Last Break	No
Glow-Wire Capable	Yes
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Mated Height	16.78mm
Material - Metal	High Conductivity Copper
Material - Plating Mating	Matte Tin
Material - Plating Termination	Matte Tin
Material - Resin	Liquid Crystal Polymer
Net Weight	4.498/g
Number of Rows	2
Orientation	Vertical
PC Tail Length	3.73mm
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.58mm
Packaging Type	Tray
Pitch - Mating Interface	5.70mm
Pitch - Termination Interface	5.70mm
Plating min - Mating	1.524µm
Plating min - Termination	1.524µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Yes
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Through Hole
Unmated Height	14.80mm

Electrical



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)4578-DC (25
June 2020)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[76829 Series](#)

Mates With

Mega-Fit Receptacle Housings [171692](#)
, [170001](#)
Mega-Fit Cable Assembly
[45136](#)

Current - Maximum per Contact
Voltage - Maximum

23.5A
600V AC (RMS)/DC

Material Info

Reference - Drawing Numbers

Application Specification

768232000-AS-000, AS-76823-100-001

Packaging Specification

768291100-000

Product Specification

PS-76823-100-001

Sales Drawing

768290002-000

Test Summary

TS-76823-100-001

This document was generated on 11/20/2020

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION