

Detailed Specifications

Frame Width:	80[mm]
Frame Height:	80[mm]
Frame Depth:	20[mm]
Max. Air Flow:	27.5[CFM]
Max. Air Flow:	0.77[m ³ per min]
Max. Static Pressure:	0.09[In H ₂ O]
Max. Static Pressure:	22.4[Pa]
Fan Speed:	2600[RPM]
Noise:	27[dB]
Life Expectancy:	60 degree C 40,000 Hours[L10]
Bearing Type:	Ball Bearing
Nominal Voltage:	24[V]
Operating Voltage 0 Lower:	9[V]
Operating Voltage 0 Upper:	27.6[V]
Current:	0.05[A]
Input Power:	1.2[W]
Mass:	79.83[g]
Tach / Locked Rotor Output:	No