


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0855075002](#)
Status: **Active**
Overview: Magnetic and Modular Jacks/Plugs
Description: Modular Jack, Cat5e, Vertical, Top Entry, Through Hole, 8/8, Int. Shielded, no Ribs, Tray

Documents:

| | |
|--|--|
| 3D Model | Packaging Specification PK-95022-001 (PDF) |
| Drawing (PDF) | RoHS Certificate of Compliance (PDF) |
| Product Specification PS-85507-001-001 (PDF) | Product Literature (PDF) |
| Application Specification AS-85513-001-001 (PDF) | |



Agency Certification

UL E107635

General

| | |
|---------------------------|--|
| Product Family | Modular Jacks/Plugs |
| Series | 85507 |
| Comments | Reflow Capable, Internal Shield |
| Component Type | PCB Jack |
| Magnetic | No |
| Overview | Magnetic and Modular Jacks/Plugs |
| Performance Category | 5e |
| Power over Ethernet (PoE) | N/A |
| Product Name | Modular Jack 8/8, RJ45 |
| UPC | 800756696638 |

Physical

| | |
|--------------------------------|--------------------------------|
| Boot Color | N/A |
| Color - Resin | Black |
| Durability (mating cycles max) | 2500 |
| Flammability | 94V-0 |
| Inverted / Top Latch | No |
| Jack Height | 16.25mm |
| Lightpipes/LEDs | None |
| Material - Metal | Phosphor Bronze |
| Material - Plating Mating | Gold over Palladium Nickel |
| Material - Plating Termination | Tin |
| Material - Resin | High Temperature Thermoplastic |
| Net Weight | 3.470/g |
| Orientation | Vertical (Top Entry) |
| PCB Locator | Yes |
| PCB Retention | Yes |
| PCB Thickness - Recommended | 1.57mm |
| Packaging Type | Tray |
| Pitch - Mating Interface | 1.02mm |
| Pitch - Termination Interface | 1.27mm |
| Plating min - Mating | 0.051µm, 1.016µm |
| Plating min - Termination | 1.905µm |
| Port Configuration | 1x1 |
| Positions / Loaded Contacts | 8/8 |
| Surface Mount Compatible (SMC) | No |
| Temperature Range - Operating | -40° to +85°C |
| Termination Interface: Style | Through Hole |
| Waterproof / Dustproof | No |
| Wire/Cable Type | N/A |

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)4578-DC (25
June 2020)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[85507](#) Series

Mates With

[95043](#) Modular Plug, Short Body

Electrical

| | |
|-------------------------------|---------|
| Current - Maximum per Contact | 1.5A |
| Grounding to PCB | Yes |
| Shielded | Yes |
| Voltage - Maximum | 125V DC |

Material Info**Reference - Drawing Numbers**

| | |
|---------------------------|------------------|
| Application Specification | AS-85513-001-001 |
| Packaging Specification | PK-95022-001 |
| Product Specification | PS-85507-001-001 |
| Sales Drawing | SD-85507-501-001 |

This document was generated on 10/13/2020

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION