







RRX3M-Z

3 pole male XLR receptacle with D-Size Flange, solder cups and IP65 protection







Features & Benefits

- D-shape metal flange
- UL94 V-0 rated materials

• IP65 rating water protection when mating with related REAN IP65 connector or with rubber Cap covered



Article Variations

Article Name	Details	Packaging
RRX3M-Z-000-0/1	Chrome plated housing, tin plated contacts	BULK / Plastic Bag
RRX3M-Z-001-0/1	Black plated housing, tin plated contacts	BULK / Plastic Bag
RRX3M-Z-002-0/1	Black plated housing, gold plated contacts	BULK / Plastic Bag



Technical Information

Product	
Title	RRX3M-Z
Connection Type	XLR
Gender	male

Electrical		
Contact resistance	$\leq 5 \text{ m}\Omega$	
Dielectric strength	1,5 kVdc	
Insulation resistance	> 10 GΩ (initial)	
Rated current per contact	16 A	
Rated voltage	< 50 V	

Mechanical	
Insertion force	≤ 60 N
Withdrawal force	≤ 60 N
Lifetime	> 1000 cycles
Wiring	Solder contacts
Locking device	Latch lock
Mounting direction	Front mounting
Chassis shape	D

Material		
Contact plating	Tin (-000 & -001) / AU (-002)	
Contacts	Brass	
Insert	Polyamide (UL94-V0)	
Locking element	Zinc diecast	
Shell	Zinc diecast	
Shell plating	Chrome (-000) / Black (-001 & -002)	



Environmental		
Flammability	UL 94-V0	
Protection class	IP65 (Mated or closed with rubber cap)	
Standard compliance	IEC 61076-2-103	
Solderability	Complies with IEC 68-2-20	
Temperature range	-20 °C to +70 °C	