

Datasheet for part number DBMM-25P

Our Catalog Part Number: DBMM-25P

Our Global Manufacturing Part Number: 051522-0000

Brand: Cannon Product Category: D Sub Product Line: D Sub Series: D*M

Product Datasheet	
General	D*M High reliable D-Sub Connectors
Wire Gauge Range AWG	AWG 20-28
Mating Cycles	500
Contact Arrangement	25 contacts size 20
Dielectric Withstanding Voltage	1000 VAC at sea level
Current Rating	7.5 A max
Contact Resistance	7.5 milli Ohm max
Operating Temperature	-55°/+150°
Salt Spray Test	48 hours {96 Hrs for Stainless Steel}
Shell Material	steel
Shell Finish	Yellow chromate over zinc
Insulator Material	Thermoplastic, type PCT UL 94V-0
Insulator Color	black
Gender	Pin
Contact Type	Solder Pot
Contact Material	copper alloy
Contact Finish	gold over nickel (Performance Class 2)
Hardware	.120" (3,05mm) Through Hole
Disclaimer	Our facility is not currently certified by the DLA and this product is not covered by the QPL/QML.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

ITT Cannon:

DBMM-25P DBMM-25P-F179 DBMM-25P-S DBMM-25P-Z DBMM-25P-B DBMM-25P-A-A159 DBMM-25P-H-A214

DBMM-25P-C DBMM-25P-M DBMM-25P-F179A DBMM-25P-D DBMM-25P-A-A101 DBMM-25P-E DBMM-25P-H

DBMM-25P-W DBMM-25P-K DBMM-25P-L DBMM-25P-X DBMM-25P-A DBMM-25P-Z-A101 DBMM-25P-F DBMM-25P-P DBMM-25P-G