

Data sheet

Commercial Art.No.: 56.198.1055.0

High current terminal WRT 185/M12

High current terminal block with ring lug connection for mounting on TS35, nominal cross section: 185 mm², Width: 55 mm, Color: grey



Commercial Art.No.	56.198.1055.0
EAN	4049088260858
Order Unit	5

Certificates / Approvals



Technical data

General

Nominal cross section	185 mm ²
Colour	Grey
Number of levels	1
Number of clamp positions per level	2
Width/grid dimension	55 mm
Insulating housing	PA66
Inflammability class of insulation material acc. with UL94	V0
Explosion-tested version "Ex e"	No
Mounting method	DIN rail (top hat rail) 35 mm
Terminal blocks for electrical installations	Yes

Technical data

Rated current	353 A
Rated voltage	1000 V
Rated impulse voltage	8 kV
Pollution degree	3
Type of insulation material	Thermoplastic
Length	164 mm
Width	55 mm
Height	78 mm

Connection Data

Connection type	Bolt connection
Connection type 1	Bolt connection
Minimum cross section fine stranded	10 mm ²
Maximum cross section fine stranded	240 mm ²

Technical Data UL/CSA

Cross section UL	AWG 10 - 500 kcmil
------------------	--------------------

Voltage UL	1000 V
Current factory wiring	380 A
Cross section CSA	AWG 10 - 500 kcmil
Voltage CSA	1000 V
Current CSA	380 A

Classification

ECLASS 8.1	27141120
ETIM 7.0	EC000897
ETIM 6.0	EC000897
ETIM 5.0	EC000897

Accessories

Commercial Art.No.:	Article-type description:	Description:
---------------------	---------------------------	--------------

Fits with

Commercial Art.No.:	Article-type description:	Description:
---------------------	---------------------------	--------------