

- ▲ CONTACT: COPPER ALLOY PER ASTM BI96 SLEEVE: STAINLESS STEEL PER AISI 305
- Δ CONTACT: I.27μm MIN GOLD PER ASTM B488 OVER 2.54μm MIN NICKEL PER QQ-N-290 ON ENTIRE STOCK.
- OPTIONAL ALTERNATE MARKING: LETTER "S"
- A RED COLOR BAND
- 5. APPLICABLE WIRE SIZE: 20-22-24 AWG WIRE INSULATION DIAMETER: 1.8 mm MAX INSULATION STRIP LENGTH: 3.65-4.15 mm
- 6. APPLICATION TOOLING: CRIMPING TOOL: TYCO PART NUMBER 601966-1 (M22520/2-01) POSITIONER: TYCO PART NUMBER 601966-5 (M22520/2-08) SELECTOR POSITION: AWG 20: 7 AWG 22: 6 AWG 24: 5 CONTACT INSERTION/EXTRACTION TOOL: 91067-2 (M81969/1-02)
- 7. THIS PRODUCT IS SOLD BY TYCO ELECTRONICS UNDER A LICENSE FROM RADIALL SA.

AMP 1471-9 REV 31MAR2000


Pro/ENGINEER DRAWING

D


С

В

А



2



				PART NUMBER
THIS DRAWING IS A CONTROLLED DOCUM IT IS SUBJECT TO CHANGE AND THE G SHOULD BE CONTACTED F	ENT FOR TYCO ELECTRONICS CORPORATION ONTROLLING ENGINEERING ORGANIZATION OR THE LATEST REVISION.	DWN 08APR2005 BW	tyco Tyco Electronics	
			Electronics Harrisburg, PA 17105-3608	
DIMENSIONS: MM	TOLERANCES UNLESS OTHERWISE SPECIFIED:		SOCKET CONTACT ASSEMBL	Υ.
	0 PLC ±- I PLC ±-	PRODUCT SPEC	SIZE 20, GPR	_ ')
3 PLC		APPLICATION SPEC		
	4 PLC ±- ANGLES ±-	_	SIZE CAGE CODE DRAWING NO	RESTRICTED TO
		WEIGHT _	A 200779 C-1738012	-
	<u>/ </u>	CUSTOMER DRAWING	SCALE 20: SHEET	OF REV

D

С

В

A

| 17380|2-|

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

TE Connectivity: <u>1738012-1</u>