


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0874370243](#)
Status: **Active**
Overview: [Pico-SPOX Wire-to-Board Connector System](#)
Description: 1.50mm Pitch, Pico-SPOX PCB Header, Single Row, Vertical, Surface Mount, Tin (Sn) Plating, Friction Lock, 2 Circuits, Tape and Reel, without Cap, Beige

Documents:

| | |
|--|--|
| 3D Model | Application Specification 874370000-AS-000 (PDF) |
| Drawing (PDF) | Packaging Specification SPK-87437-001-001 (PDF) |
| 3D Model (PDF) | Packaging Specification SPK-87438-001-001 (PDF) |
| Product Specification PS-87437-001-001 (PDF) | RoHS Certificate of Compliance (PDF) |



Series image - Reference only

Agency Certification

UL E29179

General

| | |
|----------------------|--|
| Product Family | PCB Headers |
| Series | 87437 |
| 3D Viewer | Yes |
| Application | Signal, Wire-to-Board |
| CURRENT-MAX-NUMERIC | 2.5 |
| Overview | Pico-SPOX Wire-to-Board Connector System |
| PITCH-MATING-NUMERIC | 1.50 |
| Product Name | Pico-SPOX |
| UPC | 822348438006 |

Physical

| | |
|--------------------------------|-----------------------|
| Breakaway | No |
| Circuits (Loaded) | 2 |
| Circuits (maximum) | 2 |
| Color - Resin | Beige |
| Durability (mating cycles max) | 10 |
| First Mate / Last Break | No |
| Flammability | 94V-0 |
| Glow-Wire Capable | No |
| Guide to Mating Part | No |
| Keying to Mating Part | None |
| Lock to Mating Part | Yes |
| Material - Metal | Brass |
| Material - Plating Mating | Tin |
| Material - Plating Termination | Tin |
| Material - Resin | Nylon |
| Net Weight | 129.000/mg |
| Number of Rows | 1 |
| Orientation | Vertical |
| PCB Locator | No |
| PCB Retention | None |
| Packaging Type | Embossed Tape on Reel |
| Pitch - Mating Interface | 1.50mm |
| Plating min - Mating | 2.540µm |
| Plating min - Termination | 2.540µm |
| Polarized to Mating Part | Yes |
| Polarized to PCB | No |
| Shrouded | Fully |
| Stackable | No |
| Temperature Range - Operating | -55° to +105°C |
| Termination Interface: Style | Surface Mount |

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/71/2019 (16 July 2019)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[87437 Series](#)

Mates With

[Pico-SPOX Wire-to-Board Housing 87439](#)

Electrical

Current - Maximum per Contact
Voltage - Maximum

2.5A
250V AC (RMS)/DC

Material Info**Reference - Drawing Numbers**

Application Specification
Packaging Specification
Product Specification
Sales Drawing

874370000-AS-000
SPK-87437-001-001, SPK-87438-001-001
PS-87437-001-001
874370231-SD-000, SD-87437-001-001

This document was generated on 11/11/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION