



REV.	ECN. NO.	APPD.
A		

NOTES:

Current Rating: 1.0AMP
 Withstand Voltage: 500V AC/DC
 Contact Resistance: 20mΩ Max
 Insulation Resistance: 1000MΩMin
 Operation Temperature: -40°C to +105°C

Contact Material: Phosphor Bronze
 Contact plating: Au
 Insulator Material: PA6T+30%G.F UL94V-0



Recommended P.C.B Layout(TOP Side)
 (PCB BOARD TOLERANCE±0.05)



Ordering Information

MTF344-1XXSU1

No. of Pins per ROW: 02-40PIN



SECTION B-B

X. ± 0.30	X.° ± 5°	UNITS mm	NAME (INTENDED USE)	MINTRON CO.,LTD.
.X ± 0.20	.X° ± 2°	MAT'L	PART NO. (INTENDED USE)	
.XX ± 0.10	.XX° ± 1°	FINISH	APPD: SUNNY	TITLE: FEMALE HEADER 1.27mm SINGLE 180°
.XXX ± 0.05	.XXX° ± 0.5°		CHKD: LISA	DWG NO.: MTF344-1XXSU1
FEMALE HEADER CONNECTOR		Q'TY	DR: ZOE 2006-11-28	SCALE 1/1
				SHEET 1/1
				REV. A