

Specifications

Model	Tank size	Unit size	Volume	Ultrasonic power	Ultrasonic frequency	Heating power	Timer	Heating temperature
	L×W×H(mm)	L×W×H(mm)	(L)	Normal (W)	(kHz)	(W)	(MIN)	(°C)
GT SONIC-R2	150×140×100	190×170×220	2	50	40	100	1-99	0-80
GT SONIC-R3	240×140×100	270×170×240	3	100		100		
GT SONIC-R6	300×155×150	330×180×310	6	150		300		
GT SONIC-R9	300×240×150	330×270×310	9	200		300		
GT SONIC-R13	330×300×150	360×330×310	13	300		400		
GT SONIC-R20	500×300×150	550×330×310	20	400		500		
GT SONIC-R27	500×300×200	550×330×360	27	500		500		