




Pushing Performance

Han Fast-Lock 10qmm ang.silverplate.+pin



Part number	09 08 000 7224
Specification	Han Fast-Lock 10qmm ang.silverplate.+pin
HARTING eCatalogue	https://b2b.harting.com/09080007224

Identification

Category	Contacts
Series	Han-Fast [®] Lock
Type of contact	PCB contact
Description of the contact	With pin Angled

Version

Pack contents	Single contact
---------------	----------------

Technical characteristics

Conductor cross-section	10 mm ²
Operating current	≤60 A
Contact resistance	≤2 mΩ
Stripping length	7.5 mm

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
Material (locking)	Copper alloy
Surface (locking)	Passivated
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50



Pushing Performance

Material properties

REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

Commercial data

Packaging size	100
Net weight	2.46 g
Country of origin	Germany
European customs tariff number	85366990
eCl@ss	27440402 PCB connector