

## M23 female-c 2mm (0,75 – 2,5mm<sup>2</sup>) Au



Image is for illustration purposes only. Please refer to product description.

Part number	09 15 100 6221
Specification	M23 female-c 2mm (0,75 – 2,5mm <sup>2</sup> ) Au
HARTING eCatalogue	<a href="https://b2b.harting.com/09151006221">https://b2b.harting.com/09151006221</a>

### Identification

Category	Contacts
Series	Circular connectors M23
Identification	Signal
Type of contact	Crimp contact
Description of the contact	2 mm

### Version

Gender	Female
Manufacturing process	Turned contacts

### Technical characteristics

Conductor cross-section	0.75 ... 2.5 mm <sup>2</sup>
Conductor cross-section	AWG 19 ... AWG 14
Operating current	≤20 A
Contact resistance	≤3 mΩ
Stripping length	4 mm

### Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Gold plated
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption



Pushing Performance

## Material properties

China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

## Specifications and approvals

Specifications	EN 60664-1 IEC 61984
----------------	-------------------------

## Commercial data

Packaging size	100
Net weight	0.56 g
Country of origin	Germany
European customs tariff number	85366990
eCl@ss	27440204 Contact for industrial connectors