

# Han 3A-BU-S



Part number	09 20 003 2711
Specification	Han 3A-BU-S
HARTING eCatalogue	https://b2b.harting.com/09200032711

Image is for illustration purposes only. Please refer to product description.

### Identification

Category	Inserts
Series	Han A <sup>®</sup>

#### Version

Termination method	Screw termination
Gender	Female
Size	3 A
Number of contacts	3
PE contact	Yes

## Technical characteristics

Conductor cross-section	0.75 1.5 mm²
Rated current	10 A
Rated voltage conductor-earth	230 V
Rated voltage conductor-conductor	400 V
Rated impulse voltage	4 kV
Pollution degree	3
Rated voltage acc. to UL	600 V
Insulation resistance	>10 <sup>10</sup> Ω
Stripping length	2.5 5.5 mm
Tightening torque	0.25 Nm
Limiting temperature	-40 +125 °C



### Technical characteristics

Mating cycles ≥500

## Material properties

Material (insert)	Polycarbonate (PC)
Colour (insert)	RAL 7032 (pebble grey)
Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
Material flammability class acc. to UL 94	V-0
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

### Specifications and approvals

Specifications	EN 60664-1 IEC 61984
Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076

### Commercial data

Packaging size	10
Net weight	13.35 g
Country of origin	Romania
European customs tariff number	85366990
eCl@ss	27440205 Contact insert for industrial connectors