

## Han 3A Protect Cover, Sealing Die Cast f



Image is for illustration purposes only. Please refer to product description.

Part number	09 20 003 5425
Specification	Han 3A Protect Cover, Sealing Die Cast f
HARTING eCatalogue	<a href="https://b2b.harting.com/09200035425">https://b2b.harting.com/09200035425</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han A <sup>®</sup>
Type of hood/housing	Protection cover
Description of hood/housing	for bulkhead mounted housings
	for surface mounted housings
	Metal
	With fixing cord
	With seal

### Version

Locking type	Single locking lever
Size	3 A
Field of application	Standard Hoods/housings for industrial applications
Details	for mounted female insert or for mounted Han-Brid <sup>®</sup> insert

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP44
	IP65 / IP67 with seal screw 09 20 000 9918
Type rating acc. to UL 50 / UL 50E	12

### Material properties

Material (seal)	NBR
RoHS	compliant
ELV status	compliant



Pushing Performance

## Material properties

China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

## Specifications and approvals

Approvals	DNV GL
-----------	--------

## Commercial data

Packaging size	10
Net weight	23 g
Country of origin	Romania
European customs tariff number	85389099
eCl@ss	27440208 Cap for industrial connectors