

## Han C-male contact-c 2.5mm<sup>2</sup>



Image is for illustration purposes only. Please refer to product description.

Part number	09 32 000 6105
Specification	Han C-male contact-c 2.5mm <sup>2</sup>
HARTING eCatalogue	<a href="https://b2b.harting.com/09320006105">https://b2b.harting.com/09320006105</a>

### Identification

Category	Contacts
Series	Han <sup>®</sup> C
Type of contact	Crimp contact

### Version

Gender	Male
Manufacturing process	Turned contacts

### Technical characteristics

Conductor cross-section	2.5 mm <sup>2</sup>
Conductor cross-section	AWG 14
Operating current	≤40 A
Contact resistance	≤1 mΩ
Stripping length	9.5 mm

### Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No



Pushing Performance

## Material properties

REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

## Specifications and approvals

Specifications	EN 60664-1 IEC 61984
----------------	-------------------------

## Commercial data

Packaging size	25
Net weight	3.01 g
Country of origin	Germany
European customs tariff number	85366990
eCl@ss	27440204 Contact for industrial connectors