




REVISIONS				
REV	ECO	DESCRIPTION	DATE	BY APPR
A1	-	RELEASED DRAWING	Nov-9-17	Rookie Tommy
A2	-	ADD THE GS PART NUMBER	Jan-28-19	Blink Tommy
A3	-	CHANGE HAND CRIMPER	Nov-8-19	Flan Tommy



SECTION A-A

QUANTITY	PART NUMBER	DESCRIPTION	ITEM

MATERIALS LIST			
SIGNATURES	DATE	DESCRIPTION	ITEM
DRAWN: Ril	Nov-8-19		
CHECKED: Mah	Nov-8-19		
ENGINEER: Tommy	Nov-8-19		
APPROVE: Tommy	Nov-8-19		

UNLESS OTHERWISE SPECIFIED	
1) All dimensions are in millimeters.	
2) Tolerances are as follows:	
1 Pt. DEC 40-30	Fractions 1/16"
3 Pt. DEC 20-05	Decimals .015"
3) Note reference =	

PROCESS SPECIFICATIONS	
MATERIAL SPECIFICATIONS	CUSTOMER: Tommy
	APPROVE: Tommy
	DATE: Nov-8-19

ECO-MATE SOCKET CONTACT, STAMPED, 24-26AWG, SIZE 20	
SIZE TYPE	B C-
DWG NO	SS24W2XX
SCALE	NONE
SHEET	1 OF 1

- CONTACT ORIENTATION ON ROLL
 NOTES: (UNLESS OTHERWISE SPECIFIED)
- MATERIAL:
 - CONTACT BODY: COPPER ALLOY.
 - OUTER SPRING: STAINLESS STEEL.
 - SPECIFICATIONS:
 - CURRENT RATING: 5A MAX.
 - TERMINATION TYPE: CRIMPING.
 - WIRE RANGE: 26~24AWG.
 - WIRE INSULATION DIA(MAX): Ø2.2mm.
 - ROHS COMPLIANT.
 - ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.
 - AVAILABLE TOOLS:
 - HAND CRIMPER: MFX-3958. A3
 - CRIMP APPLICATOR: MFX-3957.
 - EXTRACTION TOOL: QXRT20.

P/N	CONTACT PLATING(MATING AREA)
SS24W2T	TIN PLATING OVER NICKEL.
SS24W2N	NICKEL PLATING OVER COPPERIZE.
SS24W2F	GOLD FLASH PLATING OVER NICKEL.
SS24W2G5	5µ" GOLD PLATING OVER NICKEL.
SS24W2G10	10µ" GOLD PLATING OVER NICKEL.
SS24W2G15	15µ" GOLD PLATING OVER NICKEL.
SS24W2G30	30µ" GOLD PLATING OVER NICKEL.

A2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[SS24W2F](#)