


SECTION A-A



PCB layout

Specifications:

Current Rating:1.5A AC/DC
 Voltage Rating:30V AC/DC
 Contact Resistance:30m ohm. Max.
 Insulation Resistance:1,000M ohm. min.
 Withstanding Voltage:500V AC For One Minute
 Operating Temperature Range:-40°C ~ +105°C

Material and Finish

Insulator:PBT (UL94V-0)
 Color:White
 Contact:Brass
 Plating:30u" Gold Plated on Contact Area,
 Tin Plated on Solder Tail.
 Shell:Brass,Nickel Plated

RoHS Compliant

				DRAWN:	GENERAL TOLERANCE: .X=±0.20 .XX=±0.10	CnC Tech Industrial Cable and Connector Technology	SIZE A4
				CHECKED:	UNIT: MM SCALE:1:1		
				APPROVAL:	SHEET: 1 / 2	DESCRIPTION: USB A PCB Socket Straight, 30u"	PART NO: 1002-001-01000
REV	DATE	FILE	BY		PROJECTION:		