


## Features

- AMD Ryzen™ Embedded V1000/R1000 Series on board
- 2x DDR4 SO-DIMM, Max. 32GB
- 2x PCI-E Gigabit LAN
- 2x HDMI, 1x eDP, 1x 24-bit LVDS dual-channel
- 1x USB2.0, 4x USB3.1, 1x SATA III, 4x COM
- 2x M.2 sockets (M/ E key)




## Specifications

CPU	AMD Ryzen™ Embedded V1000/R1000 Series on board
PCH	N/A
Memory Type	DDR4-2400 SO-DIMM, Max. 32GB, supports ECC
BIOS	AMI
Watchdog Timer	256 levels
H/W Monitor	Yes
Storage Device Interface	1x M.2 (M-key)
Mini Type Slots	1x M.2 (M-key, type:2280, NVMe) 1x M.2 (E-key, type:2230)
Graphics Controller	AMD Raden™ Vega integrated
Video Output	2x HDMI(2.0a), 1x 24-bit Dual-channel LVDS & eDP
Ethernet	2x Intel® I211AT PCI-E Gigabit LAN
I/O Chip	Fintek F81964D-I
Serial Port	1x RS232/422/485 (Jumper-less selection) 3x RS232
USB 2.0	1x USB 2.0 on board
USB 3.0/ 3.1	4x USB 3.1 on board
Serial ATA	1x SATA III
Audio	Built-in audio w/ Realtek ALC269Q-VC3-GR w/ class-D amplifier
TPM	TPM (2.0)
Others	Digital I/O(4-in/ 4-out), EuP/ErP, +12V~+24V DC-in (+/-10%)
Dimensions (L x W)	102mm x 147mm (4" x 5.8")
Power Consumption	AMD Ryzen™ Embedded V1605B 2.00GHz w/ 2x 16GB DDR4-2400 +12V: 2.55A AMD Ryzen™ Embedded R1606G 2.6GHz w/ 2x 16GB DDR4-2400 +12V: 2.34A
Operating Temperature	0°C~60°C (32°F~140°F)
Storage Temperature	-20°C~80°C (-4°F~176°F)
Relative Humidity	90% (non-condensing@60°C)

## Ordering Information

IB918F-1605	AMD Ryzen™ V1605B QC APU (2.0GHz~3.6GHz) on board 3.5-inch Disk-Size w/ dual LAN, 2x HDMI, eDP & LVDS (24-bit dual-channel), EuP/ErP, 12V~24V DC-in
IB918F-1202	AMD Ryzen™ V1202B DC APU (2.3GHz~3.3GHz) on board 3.5-inch Disk-Size w/ dual LAN, 2x HDMI, eDP & LVDS (24-bit dual-channel), EuP/ErP, 12V~24V DC-in
IB918F-1606G	AMD Ryzen™ R1606G DC (2.6GHz~3.5GHz) on board 3.5-inch Disk Size w/ dual GbE LAN, 2x HDMI (2.0a), eDP, EuP/ErP, 12V~24V DC-in
IB918F-1505G	AMD Ryzen™ R1505G DC (2.4GHz~3.3GHz) on board 3.5-inch Disk Size w/ dual GbE LAN, 2x HDMI (2.0a), eDP, EuP/ErP, 12V~24V DC-in
HSIB918-A	Heat sink with fan for IB918
HSIB918-1	Heat spreader for IB918
IB90	Cable kit w/ PW87,PK1H,SATA-53A,USB-168 for V1000 series
IB91	Cable kit w/ PW87,PK1H,SATA-53A,USB-172 for R1000 series

## Dimensions and Drawing



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[IBASE:](#)

[IB918F-1202](#) [IB918F-1505G](#) [IB918F-1605](#) [IB918F-1606G](#)