

Coaxial Cable Connector 21_UHF-0-7-4/033_

Description

Straight cable jack

Interface standards
IEC 60169-12



Technical Data

Electrical Data

Impedance other Ω
Interface frequency max. 0.2 GHz

Mechanical Data

Centre contact crimped
Outer contact crimped
Weight 0.0324 kg

Environmental Data

Operating temperature -55 °C to 165 °C
2011/65/EU (RoHS - including
2015/863 and 2017/2102) compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Silver Plating
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Crimp ferrule	Copper	SUCOPLATE (R) Plating

Related Documents

Outline drawing DOU-00007985
Catalogue drawing DCA-00006309
Assembly instruction DOC-0000201061

Ordering Information

Single package 21_UHF-0-7-4/033_E

Additional Information

Suitable cables RG_213_/U, GX_07272, G_07262, G_07272, RADOX_RF_213

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HUBER+SUHNER:](#)

[21_UHF-0-7-4/033_-E](#)