



UNIT:MM

REVISION INFORMATION			
Rev.	Rev. Date	Modified By	Brief Description
A/0	18-08-07	T0806A	NEW DRAWING



PIN ASSIGNMENT:

P1		P2
1	RED	1
2	WHITE	2
3	GREEN	3
4	BLACK	4
SHELL	DRAIN	SHELL


Electrical test:

- 100% short, open, miswire test
- Conduct resistance: 2 Ohm(max)
- Insulation resistance: 20Mohm(min)
- dielectric test: DC 300V

CABLE WHITE PRINT

E166160 AWM 2725 80°C 30V
28AWGX1P+24AWGX2C USB2.0

PART NO	WIRE LENGTH "L"	BUYER COLOR	VENDOR COLOR	CUT LENGTH
102-1010-BL-00180	1800±50		BLACK	1780-1800MM



④	PE BAG	1/10	CLEAR SIZE:280X330X0.05mm PRINT BLACK"MADE IN CHINA"+"10PCS"
⑧	PE BAG	1	CLEAR SIZE:130X230X0.05mm PRINT BLACK"MADE IN CHINA"
⑦	TIE	1	WHITE L=100mm
⑥	IN JACKET	3g	CLEAR LDPE(MOULD NO:NM-027)
⑤	OUT JACKET	7g	BLACK PVC-40P (MOULD NO:WM-83)
④	OUT JACKET	6g	BLACK PVC-40P (MOULD NO:2002-527)
③	CABLE	1	BLACK USB2.0 UL2725 28#/1P+24#/2C+AEB OD:4.7mm
②	CONN	1	USB2.0 A FEMALE SHELL:NICKEL PIN G/F SHORT TYPE INSULATOR COLOR:WHITE
①	CONN	1set	USB2.0 A MALE SHELL:MICKEL PIN G/F 3PCS-TYPE INSULATOR COLOR:WHITE

NO.	NAME	QTY	SPECIFICATION
-----	------	-----	---------------

CnC Tech, LLC
Industrial Cable and Connector Technology

DRAWN BY:	DATE: 2018/08/07	DESCRIPTION: 4C CABLE USB A/M+A/F
CHECKED BY:	SHEET 1 of 1	ITEM NO. As above
APPROVED BY:	SCALE 1:1	REV. A/0
	UNIT: mm	