


**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1054440001](#)  
**Status:** **Active**  
**Overview:** [USB Products and Solutions](#)  
**Description:** Universal Serial Bus (USB) Shielded I/O Plug, Type C, Right-Angle, Surface Mount, 0.76µm Gold (Au) Plating, Tray

**Documents:**

<a href="#">3D Model</a>	<a href="#">Packaging Specification 1054440001-PK (PDF)</a>
<a href="#">3D Model (PDF)</a>	<a href="#">Test Summary 1054440001-TS (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Product Specification 1054440001-000 (PDF)</a>	



**General**

Product Family	I/O Connectors
Series	<a href="#">105444</a>
Application	Wire-to-Board
Comments	Nickel underplating
Component Type	Plug
Overview	<a href="#">USB Products and Solutions</a>
Product Name	USB 3.1
Type	C
UPC	191128091886

**Physical**

Circuits (Loaded)	22
Circuits (maximum)	22
Color - Resin	Black
Durability (mating cycles max)	10000
Gender	Male
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	0.633/g
Number of Rows	2
Orientation	Right Angle
PCB Locator	Yes
PCB Retention	None
PCB Thickness - Recommended	0.80mm
Packaging Type	Tray
Panel Mount	Yes
Pitch - Mating Interface	0.50mm
Pitch - Termination Interface	0.50mm
Plating min - Mating	0.762µm
Plating min - Termination	3.048µm
Polarized to Mating Part	No
Polarized to PCB	Yes
Ports	1
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-30° to +85°C
Termination Interface: Style	Surface Mount

**Electrical**

Current - Maximum per Contact	0.25A, 1.25A, 5.0A
Grounding to Panel	None

**EU ELV**

**Compliant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2020)9139-DC (19  
Jan 2021)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Compliant

Not Contained

**Search Parts in this Series**

[105444 Series](#)

**Mates With**

USB Type C Receptacle

Shield Type	Full Shield
Shielded	Yes
Voltage - Maximum	30V AC (RMS)

**Material Info**

**Reference - Drawing Numbers**

Packaging Specification	1054440001-PK
Product Specification	1054440001-000
Sales Drawing	1054440001-SM
Test Summary	1054440001-TS

This document was generated on 03/23/2021

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**