

EW 15/2**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product image**Klippon® Connect with clamping yoke Technology**

The high reliability and variety of designs of the terminal blocks with clamping yoke connections make planning easier and optimises operational safety. Klippon® Connect provides a proven response to a range of different requirements.

General ordering data

Version	Accessories, End bracket
Order No.	1071900000
Type	EW 15/2
GTIN (EAN)	4008190462949
Qty.	50 pc(s).

Creation date November 25, 2020 4:59:30 PM CET

Catalogue status 20.11.2020 / We reserve the right to make technical changes.

EW 15/2**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Depth	25 mm	Depth (inches)	0.984 inch
Height	27 mm	Height (inches)	1.063 inch
Net weight	5.2 g	Width	8 mm
Width (inches)	0.315 inch		

Material data

Material	Plastic	Colour	dark beige
UL 94 flammability rating	V-0		

System specifications

Version	For the terminals	Rail	TS 15
---------	-------------------	------	-------

Additional technical data

Interlock	for screw fixing	Type of mounting	Direct mounting
-----------	------------------	------------------	-----------------

Conductors for clamping (rated connection)

Blade size	0.6 x 3.5 mm
------------	--------------

Dimensions

TS 15 offset	13.5 mm
--------------	---------

General

Rail	TS 15
------	-------

Classifications

ETIM 6.0	EC001041	ETIM 7.0	EC001041
eClass 9.0	27-14-11-35	eClass 9.1	27-14-11-35
eClass 10.0	27-14-11-35	eClass 11.0	27141135

Approvals

ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	CAT 1 TERM 16/17 EN
Engineering Data	22353_EW_15-2_DXF.dxf STEP
Engineering Data	EPLAN, WSCAD
User Documentation	StorageConditionsTerminalBlocks