

UNION CE Range

CE24V

Rack & Pinion Closer



Application:

Ideal replacement for template closers like Briton 1110 – easy upgrade to a variable wind in/out

Excellent first fit product

- Suitable for fire resistant doors and other internal doors
- Also suitable for use with access control systems
- Sizes EN 2-4 wind through adjustment



Specification:

- Aluminium body which covers foot print of most common models
- Independent door speed and latch controls
- Adjustable backcheck for greater safety when in use
- Wind in/out closing force adjustment gives easy altering of closing force on site during install and during rest of lifetime
- Non-handed for maximum flexibility
- Adjustable, flatarm armset
- Supplied complete with tested parallel arm bracket and all fixing screws
- Easy-to-use template and pictorial fitting instructions for all fixing positions
- Universal – fully tested for fitting in Regular (Fig 1), Transom Mount (Fig 61) or Parallel Arm (Fig 66) positions
- 10 year warranty

Standards:

- Fully tested to EN 1154 in all fixing positions (full classification below)
- Suitable for use on doors 1100mm wide and weighing up to 80kg
- Included in fire test and assessed for FD 30, FD 60 and FD120 timber fire doors with intumescent protection

3	8	4/2	1	1	3
---	---	-----	---	---	---



Finish:

- Body, armset, parallel arm bracket and trim plate painted silver
- Complements both aluminium and stainless steel hardware
- Discrete UNION branding on trim plate

Variants:

Code	Description
J-CE24V-SIL	UNION CE MARKED VARIABLE SIZE 2-4 R&P CLOSER SIL