

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION



REVISIONS

© COPYRIGHT - By -

ALL RIGHTS RESERVED.

P	LTR	DESCRIPTION	DATE	DWN	APVD
	M3	REVISED PER ECO-11-004820	11MAR11	RK	HMR
	M4	REVISED PER ECO-17-014338	20APR2018	RS	DR

AMP WIRE RANGE	 Listed FILE E13288	 LR7189 Certified
16-14 AWG SOLID OR STRANDED	16-14 AWG SOLID OR STRANDED	16-14 AWG SOLID OR STRANDED



- 1 WIRE INSUL DIA,
2.921-4.318[.115-.170]
- 2 NOTE DELETED

I	50	LOOSE PIECE, BAG	8-34071-5
I	5	LOOSE PIECE, BLS	8-34071-4
I	100	LOOSE PIECE, BOX	8-34071-1
2	2500	ON TAPE, REEL	2-34071-3
2	1000	LOOSE PIECE	2-34071-2
I	2500	ON TAPE, REEL	2-34071-1
I	1000	LOOSE PIECE	34071
STYLE	QTY	PACKAGE TYPE	PART NO

AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS

MAX RECOMMENDED OPERATING
TEMPERATURE:


105°C [221° F]

VOLTAGE RATING:
600V MAX
(1000V FIXTURE OR SIGN)

CIRCULAR MIL AREA:
1.04-2.62mm²[2,050-5,180]
SOLID OR STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]



TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC	± -
1 PLC	± -
2 PLC	± -
3 PLC	± 0.127[.005]
4 PLC	± -
ANGLES	± -

MATERIAL
BODY, CU ASTM B 152
INSULATION: PVC

FINISH
BODY:TIN PLATE ASTM B545
INSULATION: COLOR-BLUE

DWN	M ELLIS	19JUL95
CHK	C PRESNELL	19JUL95
APVD	S BORTNER	19JUL95
PRODUCT SPEC	UL486A-B	
APPLICATION SPEC	114-2161	
WEIGHT	A3 00779 C=34071	
CUSTOMER DRAWING		

STE TE Connectivity Ltd.

SPLICE, BUTT, PLASTI-GRIP
WIRE SIZE 16-14 AWG

NAME	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
	A3	00779	C=34071	-
SCALE	SHEET		REV	
4:1	1 OF 1		M4	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-34071-3](#)