

- CONNECTOR
 - MXM Connector
 - M5/8/12/23 Circular Sensor Connector
 - Sealed I/O connector
 - M.2 (NGFF) Connector
 - SO DIMM Socket
 - Mini PCI Socket
 - Flash Memory Card Socket
 - CFast-CFast Card Series
 - CF-Compact Flash Card Series
 - SD-Secure Digital Card Series
 - Micro SD Socket Series
 - Micro SD with SIM Socket
 - SIM Card Socket
 - Micro SIM Card Socket
 - Nano SIM Card Socket
 - Smart Card Socket
 - FPC Connector
 - HDMI Connector
 - RJ45 Connector
 - Pogo Pin Connector
 - USB / USB COMBO Connector
 - SPDIF Jack
 - SFP/ SFP+/ QSFP
 - SFP/ SFP+/ QSFP Transceiver
 - RF Connector
 - DC High Power
 - Test Fixture
 - OBDDII Connector
- CABLE

CONNECTOR > Flash Memory Card Socket > Micro SD Socket Series



112C-TBAR-R02
Micro SD Socket Hinge Type

MATERIALS

HOUSING: HI.-TEMP PLASTIC(UL 94V-0). BLACK.
 TERMINAL: COPPER ALLOY. GOLD PLATED OVERALL (T=0.15)
 FORK: STAINLESS STEEL(t=0.20mm) TIN PLATED OVERALL
 SHELL: STAINLESS STEEL(t=0.20mm)

- PDF
- 3D

SPECIFICATION

CURRENT RATING: 0.5 A MAX.
 DIELECTRIC WITHSTANDING VOLTAGE: 500V AC R.M.S. FOR ONE MINUTE.
 INSULATION RESISTANCE: 1000M Ω MIN. AT 500V DC.
 CONTACT RESISTANCE: 30 mΩ MAX.
 OPERATING TEMPERATURE: -40°C TO +85°C

Order / Inquiry Information: (Please select Items below for Inquiry.)

Please tell us about you and your company

*Company	<input type="text"/>	*E-mail	<input type="text"/>
*Your Name	<input type="text"/>	Title/Position	<input type="text"/>
*Telephone	<input type="text"/>	FAX	<input type="text"/>
Web URL	<input type="text"/>	Business Type	<input type="text"/>
Country	<input type="text" value="Select"/>	Post Code	<input type="text"/>
Address			
<input type="text"/>			
Comments			
<input type="text"/>			
*Auth Code	<input type="text"/>	d a d 3	

Inquiry

[Back](#)

