

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1201000001](#)  
**Status:** **Active**  
**Overview:** PROFIBUS Solutions  
**Description:** Micro-Change (M12) Field Attachable Connector, PROFIBUS Shielded, Straight Female

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Field Attachable / Accessories
Series	<a href="#">120100</a>
IP Rating	IP67
Material - Contact	Brass
Overview	<a href="#">PROFIBUS Solutions</a>
Product Name	Micro-Change (M12), PROFIBUS
Type	Field Attachable Connector
UPC	78678850053

**Physical**

Cable Diameter	N/A
Coupling Type	Internal Thread
Diagnostics / LEDs	No
Diagnostics Port	No
Gender	Female
Keyway	Reverse
Material - Connector Body	N/A
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Silver
Net Weight	51.255/g
Orientation	Straight
Poles	5
Temperature Range - Operating	-25°C to +90°C
Wire Size AWG	22

**Electrical**


Current - Maximum per Contact	4.0A
Voltage - Maximum	250V

**Material Info**

Engineering Number	BA5S00-32
--------------------	-----------

**Reference - Drawing Numbers**

Sales Drawing	1201000001-000
---------------	----------------



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Contained Per -  
ED/30/2017 (7 July  
2017)

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

**Search Parts in this Series**

[120100 Series](#)