

[Find by Feature](#)
[Browse by Category](#)
[Share](#)

Enter part number or keyword

[Search Results \(95\)](#)
[Search Options](#)

95 Results:

1 2 3 4


12110127 Female Metri-Pack 800 Silver Plated Terminal, Cable range 5.00 mm2


[12110127 FLRY-B 4,0 S](#)
[12092400 CONN 3 F M/P 800 BLK](#)
[12146037 CONN 2 F M/P 800 BLK](#)
[12146038 CONN 2 F M/P 800 GRAL T](#)
[12160605 CONN 2 F M/P 800 GRN LT](#)
[12160606 CONN 2 F M/P 800 BRN](#)
[12160893 CONN 1 F M/P 800 BLK](#)
[13528106 ASM CONN 40 F GT 150 280 M/P 800](#)
[13855004 ASM CONN 72 F GT 150 280 M/P 800 MICRO 64](#)

1 2 3 4

Keyword: 12110127

Female Metri-Pack 800 Silver Plated Terminal, Cable range 5.00 mm2 Part #12110127


[Attributes](#)
[Documents \(5\)](#)
[Related Products \(2\)](#)

Part #:	12110127
Description:	Female Metri-Pack 800 Silver Plated Terminal, Cable range 5.00 mm2
Product Type:	Terminal
Status:	Active
Blade size [mm]:	8.0
Terminal family:	Metri-Pack
Series:	800
Gender:	Female
Sealed:	Unsealed
Plating:	Silver
Minimum Cable Core Cross Section [mm2]:	5.00
Maximum Cable Core Cross Section [mm2]:	5.00
Minimum Cable Diameter [mm]:	3.52
Maximum Cable Diameter [mm]:	4.48
Current range [A]:	60
Temperature range []:	-40 to 125

Certain products listed on this website may be subject to restricted usage or distribution or may not be available. For additional information, please contact your local sales office.