

Aptiv Connection Systems Catalog

Customer Service

Samples Request

Find by Feature

Browse by Category

Browse by Application

Comparison List (0)

Share

Search

Enter part number or keyword

Search Results (1)

Search Options

1 Result(s): [All] - 12124580

Compare

12124580 - Weather Pack Female Sealed Tin Plating Tang Terminal, Cable Range 1.00 - 2.00 mm2


Compare

Weather Pack Female Sealed Tin Plating Tang Terminal, Cable Range 1.00 - 2.00 mm2

Part # 12124580

[Question about this product?](#)

Attributes	Documents (2)	Related Products (1)
Part # :	12124580	
Description :	Weather Pack Female Sealed Tin Plating Tang Terminal, Cable Range 1.00 - 2.00 mm2	
Product Type :	Terminal	
Status :	✔ Active	
Terminal Family :	W/P	
Gender :	Female	
Sealable :	Sealed	
Material :	CuSn3Zn9	
Weight [g] :	1	
Plating :	Tin	
Minimum Cable Diameter [mm] :	3.96	
Maximum Cable Diameter [mm] :	3.96	
Minimum Cable Core Cross Section [mm2] :	1.00	
Maximum Cable Core Cross Section [mm2] :	2.00	
Temperature Range :	-40 to 125	
Voltage Drop :	Less than 3.0	
RoHs compliant :	✔ Yes	
ELV compliant :	✔ Yes	



Certain products listed on this website may be subject to restricted usage or distribution or may not be available. For additional information, please contact your local sales office.