

[Find by Feature](#)
[Browse by Category](#)
[Share](#)


Enter part number or keyword






Search Results (346)

[Search Options](#)

346 Results:

1 2 3 4

### 12191819 TERM F GT 150 SN SEALED


-  [12191819 FLRY-B 1,0 S VERSION V](#)
-  [12191819 FLU7Y-A 0,75 S VERSION III](#)
-  [12191819 FLRY-B 0,75 to 1,0 S VERSION I](#)
-  [12191819 FLRY-B 0,75 to 1,0 S Version II](#)
-  [12191819 FLRY-B 0,75 to 1,0 S Version III](#)
- [10737721 ASM CONN 2 F GT 150 BLK SLD](#)
- [13848313 ASM CONN 24 F GT 150 280 SLD](#)
- [13522004 CONN 3 F GT 150 BLK SLD](#)
- [13519911 CONN 5 F GT 150 GRA DK SLD](#)

1 2 3 4

Keyword: 12191819

## TERM F GT 150 SN SEALED

### Part #12191819


[Attributes](#)
[Documents \(10\)](#)
[Related Products \(1\)](#)

|   |                         |
|---|-------------------------|
| <b>Part #:</b>  | 12191819                |
| <b>Description:</b>                                       | TERM F GT 150 SN SEALED |
| <b>Product Type:</b>                                      | Terminal                |
| <b>Status:</b>  | Active                  |
| <b>Blade size [mm]:</b>                                   | 1.5                     |
| <b>Terminal family:</b>                                   | GT                      |
| <b>Series:</b>  | 150                     |
| <b>Gender:</b>  | Female                  |
| <b>Sealed:</b>  | Sealed                  |
| <b>Material:</b>  | Tin Brass               |
| <b>Plating:</b>   | Tin                     |
| <b>Minimum Cable Core Cross Section [mm<sup>2</sup>]:</b> | 0.75                    |
| <b>Maximum Cable Core Cross Section [mm<sup>2</sup>]:</b> | 1.00                    |
| <b>Minimum Cable Diameter [mm]:</b>                       | 1.70                    |
| <b>Maximum Cable Diameter [mm]:</b>                       | 2.25                    |
| <b>Current range [A]:</b>                                 | 15                      |
| <b>Temperature range [°C]:</b>                            | -40 to 125              |

Certain products listed on this website may be subject to restricted usage or distribution or may not be available. For additional information, please contact your local sales office.