

## Housing - HC-STA-D07-BWS-PL-BK - 1419265


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Panel mounting base D7, With single locking latch, Material: PA, Height: 25.5 mm, Cable gland: none, Gland: no, Standard



### Key Commercial Data

Packing unit	1 STK
GTIN	 4 055626 160160
GTIN	4055626160160
Weight per Piece (excluding packing)	0.010 g
Custom tariff number	85389099
Country of origin	China

### Technical data

#### Dimensions

Height	25.5 mm
Width	34.2 mm
Length	24.2 mm
Length of the assembly cutout	21.5 mm
Width of the assembly cutout	21.5 mm

#### Ambient conditions

Degree of protection of housing (IP)	IP66
Degree of protection of housing (NEMA)	12 (UL 50e)
Ambient temperature (operation)	-40 °C ... 125 °C

#### General

# Housing - HC-STA-D07-BWS-PL-BK - 1419265

## Technical data

### General


Note	for contact inserts HC-A03, A04, D07, D08, Q02, Q03, Q04, Q05, Q07, Q12
Size	D7
Housing type	Panel mounting base
Color	black
Locking type	With single locking latch
Screw connection	none
Housing material	PA
Seal material	NBR
Material lock	PA
Flammability rating according to UL 94	V0

### Standards and Regulations


Flammability rating according to UL 94	V0
--	----

## Drawings

Dimensional drawing



Dimensional drawing



Panel cutout

## Approvals

Approvals

Approvals


EAC

Ex Approvals

## Housing - HC-STA-D07-BWS-PL-BK - 1419265

### Approvals

#### Approval details

EAC		EAC-Zulassung
-----	---	---------------