

[Find by Feature](#)
[Browse by Category](#)
[Share](#)

Enter part number or keyword

Search Results (120)

[Search Options](#)

120 Results:

1 2 3 4

15326267 TERM F GT 150 SN SEALED

 [15326267 FLRY-A 0,75 S VERSION II](#)
 [15326267 R3 1,0 S Version I](#)
 [15326267 FLRY-B 0,75 to 1,0 S VERSION I](#)
 [15326267 FLRY-B 0,75 to 1,0 S VERSION II](#)
 [15326267 KBE-R2 0,75 to 1,0 S](#)
 [15326267 KBE-R2 0,75 to 1,0 S Version II](#)
[15305350 TERM F GT 150 SN SEALED](#)
[13842193 ASM CONN 2 F GT 150 SLD](#)
[13846843 CONN 3 F GT 150 BLK SLD](#)

1 2 3 4

Keyword: 15326267

TERM F GT 150 SN SEALED

Part #15326267
[Attributes](#)
[Documents \(11\)](#)
Part #: 15326267

Description: TERM F GT 150 SN SEALED

Product Type: Terminal

Status: Active

Blade size [mm]: 1.5

Terminal family: GT

Series: 150

Gender: Female

Sealed: Sealed

Material: Tin Brass

Plating: Tin

Minimum Cable Core Cross Section [mm²]: 0.75

Maximum Cable Core Cross Section [mm²]: 0.80

Minimum Cable Diameter [mm]: 1.70

Maximum Cable Diameter [mm]: 2.02

Current range [A]: 15

Temperature range [°C]: -40 to 125

Certain products listed on this website may be subject to restricted usage or distribution or may not be available. For additional information, please contact your local sales office.