



## TE CONNECTIVITY (TE) JC6-Q208-02=JC6 SERIES TERMINA

Buchanan | [JC6 Series](#)

1546842-2  
 TE Internal Number: 1546842-2  
 Alias ID: JC6-Q208-02

[EU RoHS Compliant](#)  
[EU ELV Compliant](#)

Barrier Style **Dual Barrier**

Bottom Termination Style **Quick Connects**

Current Rating (A) **20**

Number of Positions **2**

Centerline (Pitch) **9.53mm [.375in]**  
[See All Features](#)

✓ Active

↓ **PRODUCT DRAWING**  
English

↓ **3D PDF**

> [See All Documentation](#)

North America ▼

DISTRIBUTOR	QUANTITY	DATE AS OF
<b>MASTER ELECTRONICS CORP.</b> 1-888-473-5297	1,200	2017/09/26

<a href="#">GET SAMPLE</a>	
<a href="#">SAVE TO LIST</a> ▼	
<a href="#">CHECK FOR TOOLING</a>	
<a href="#">FIND SIMILAR PRODUCTS</a>	

### DOCUMENTATION    FEATURES    PRODUCT COMPLIANCE

#### Product Drawings

[JC6-Q208-XX ASSEMBLY](#)  
 PDF **(TIFF AVAILABLE)**  
**English**

#### CAD Files

[Customer View Model](#)  
 2D\_DXF.ZIP  
**English**

[3D PDF](#)  
 PDF  
**3D**

[Customer View Model](#)  
 3D\_IGS.ZIP  
**English**

[Customer View Model](#)  
 3D\_STP.ZIP

Please review product documents or [contact us](#) for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

## Product Type Features

Block Style **Open Bottom with Standoffs**Product Type **Barrier Strip**

## Configuration Features

Number of Positions **2**Number of Rows **1**Number of Levels **1**

## Electrical Characteristics

Current Rating (A) **20**Voltage (V) **300**

## Body Features

Barrier Style **Dual Barrier**Color **Black**

## Contact Features

Terminal Plating Finish **Bright**Terminal Material **Copper Alloy**Terminal Plating Material **Tin**

## Termination Features

Bottom Termination Style **Quick Connects**

## Mechanical Attachment

Connector Mounting Type **Panel**Screw Size **6-32**Mounting Ears **With**Mounting Options **End Mounting Ears**Screw Material **Steel**Screw Plating Material **Zinc Chromate**Top Hardware **Wire Clamp Combo Head**

Mounting Insert **Without**

Screw Head Type **Wire Clamp Combo Head**

Mounting Angle **Vertical**

#### Housing Features

Centerline (Pitch) **9.53 mm [ .375 in ]**

Housing Material **Thermoplastic**

#### Dimensions

Wire Range **22 – 12AWG [ .3 – 3 mm<sup>2</sup> ]**

Length **36.55 mm [ 1.439 in ]**

#### Industry Standards

UL Flammability Rating **UL 94V-0**

#### Packaging Features

Packaging Method **Package**

Packaging Quantity **200**

#### Other

Comment **Other options available upon request, consult our Product Information Center.**

#### Statement of Compliance

[Statement of Compliance](#)  
PDF

Compatible Products

[Contact Product Support](#)

Also in the Series | [JC6 Series](#)



[Barrier Strips \(2135\)](#)

Customers Also Bought

[SOLDER D-SUB CONNECTORS](#)

[RECTANGULAR POWER CONNECTORS](#)

[SURFACE MOUNT RESISTORS](#)

[CHASSIS PANEL MOUNT RESISTORS](#)



**9 Plug Solder Cup, 30 gold, Ro**  
5-747904-5



**MBXL VERT RCPT 3P+24S+3P**  
1-6450140-0



**RLP73M 1J R068 5% 5K RL**  
RLP73M1JR068JTD



**TE 2000W 8R2 5% Bracket**  
TE2000B8R2J

About TE Connectivity

For Partners

Customer Support

**CALL US**

**LIVE CHAT**

United States

Our Company

Events

TE News Center

Careers


Investors

Corporate Responsibility

Terms and Conditions of Sale

Distributors

Suppliers

 Email or Call Us

 Find Authorized Distributors

 What's New on TE.com

 Product FAQs

Select Country & Language

United States (EN)

Germany (DE)

China (中文)

Japan (日本語)

Afghanistan (EN) ▼

Find Your Country ▼

[Terms of Use](#) | [Privacy](#) | [Cookie Policy](#) | [Accessibility](#) | [Site Map](#)



© 2017 TE Connectivity Corporation. All Rights Reserved