

# 1571984-1 Product Details

[Share](#) | [Print](#) | [Email](#)


## Slide Switches

TSS11DGRA04=SLIDE SWITCH SPDT

**1571984-1**

TE Internal Number: 1571984-1

Active

[View 3D PDF](#)

**Product Highlights** [View All](#)

- 2 Positions
- Single Pole - Double Throw Configuration (Pole-Throw)
- Actuator Style = Extended, Side
- Actuator Color = Black
- TSS Series

- [Pricing & Availability](#)
- [Request Sample](#)
- [Add to My Part List](#)
- [Buy Product through Distributor](#)

Feedback

[Documents](#) | [Features](#) | [Compliance](#)

**Please Note:**  
Use the Product Drawing for all design activity

Product Type Features	
Actuator Style	Extended, Side
Mount Angle	Right Angle
Terminal Configuration	Standard
Electrical Characteristics	
Contact Rating	0.4 VA max @ 20 VDC or peak AC
Termination Features	
Termination Type	PC
Dimensions	
PCB Tail Length (mm [in])	3.30 [0.130]
Body Features	
Actuator Color	Black
Mount Style	Through-Hole
Actuator Material	Polyester
Contact Features	
Contact Plating	Gold
Contact Base Material	Copper

Configuration Features	
Number of Positions	2
Configuration (Pole-Throw)	Single Pole - Double Throw
Operating Function	On None On
Number of Actuators	Single
Industry Standards	
RoHS/ELV Compliance	RoHS compliant, ELV compliant
Lead Free Solder Processes	Wave solder capable to 260°C, Wave solder capable to 240°C, Wave solder capable to 265°C
RoHS/ELV Compliance History	Always was RoHS compliant
UL Flammability Rating	UL 94V-0
Identification Marking	
Stamped Marking	With
Other	
Series	TSS
Brand	TE Connectivity

**Related Products**

Not quite the product you're looking for?  
[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)