

Coaxial Cable Connector 16_MM CX-50-1-4/111_O

Description

Right angle cable plug

Interface standards
SUHNER-MM CX



Technical Data

Electrical Data

Impedance 50 Ω
Interface frequency max. 6 GHz

Mechanical Data

Centre contact soldered
Outer contact soldered
Outer contact 0.0007 kg

Environmental Data

Operating temperature -55 °C to 155 °C
2011/65/EU (RoHS) compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	Gold Plating (without Nickel underplating)
Body	Brass	Gold Plating (without Nickel underplating)
Insulator	PFA / PTFE	

Related Documents

Catalogue drawing DOU-00006007
Assembly instruction DOC-0000179220

Ordering Information

Single package 16_MM CX-50-1-4/111_OE
Bulk 100 pcs package 16_MM CX-50-1-4/111_OH

Additional Information

Suitable cables EZ_47_TP_M17, SUCOFORM_47_CU