



# DC axial fans

Series 3250 JU 92 x 92 x 38 mm



### Highlights:

- Motor protection against reverse polarity and locking.
- Air exhaust over struts
- Connection via 310 mm strands AWG 24, TR 64, bared and tin-plated
- Ingress protection rating of IP68



**Material:** Housing: Fiberglass-reinforced PBT composite  
Impeller: Fiberglass-reinforced PA composite

**Direction of rotation:** Clockwise, seen on rotor

### Nominal Data

Type	Air flow CFM	Nominal voltage VDC	Voltage range VDC	Sound pressure level dB(A)	Sound power level Bel(A)	Ball bearings	Power input Watts	Speed RPM	Temperature range °C	Mass g	Ingress Protection Rating	UL Approval	Curves
3258 J/2HHPU	<b>138.3</b>	48	36...56	59	7.2	Yes	24.3	6650	-20...70	240	IP68	Yes	1
3258 J/2H3PU	<b>158.9</b>	48	36...56	64	8.0	Yes	33.6	7450	-20...70	240	IP68	Yes	2

### Curves



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ebm-papst:](#)

[3258J/2HHPU](#) [3258J/2H3PU](#)