

(2,54mm) .100"
BBS, BBL, BHS, BBD, BDL SERIES

MACHINED BOARD STACKING STRIPS

Mates with:
 SS, SD, HSS, SL, SDL,
 ESS, ESD

FEATURES

- Low profile design achieves (3,89mm) .153" board spacings when mated with SL series.
- Choice of precision machined (BXX Series) or coined (LBS Series) terminals.
- Approach the reliability of a permanent connection with the flexibility of a separable connection.

SPECIFICATIONS

For complete specifications see www.samtec.com?BBS, www.samtec.com?BBD, www.samtec.com?BBL or www.samtec.com?BDL

BBS, BBD, BBL, BDL



Insulator Material:
 Black Glass Filled Polyester (BBS, BBD, BBL)
 Black High Temp Nylon (BDL)

Temperature Range:
 -55°C to +125°C

Terminal Material:
 Phosphor Bronze or Brass

Plating:
 Au or Sn over 50µ" (1,27µm) Ni

Current Rating:
 1A

RoHS Compliant:
 Yes

Lead-Free Solderable:
 Yes

Wave only

SPECIFICATIONS

For complete specifications see www.samtec.com?BHS

BHS

Same as BBS except:





Insulator Material:
 Black Liquid Crystal Polymer

RoHS Compliant:
 Yes

Lead-Free Solderable:
 Wave, or reflow with all Au

Wave, or reflow with all Au

Note: Some lengths, styles and options are non-standard, non-returnable.



Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM