



B198

**BahcoFit Hex Head Nut Drivers
with Rubber Grip 4-14 mm**



PRODUCT DETAILS








- Nut driver with slim bore for hexagon head screws, bolts and nuts
- Two-component handle with vertical grooves and large soft-grip area for comfortable grip and high torque transfer
- Handle made with over 75% rubber
- Permanent symbol and markings on the handle for quick identification of the tip
- Integrated hanging hole
- Chrome plated blade for high protection against corrosion, long life tool
- High-performance alloy steel blade
- SB coding for retail packed on a plastic hanger



Follow the Fish!



PRODUCT ATTRIBUTES

Product							
B198.040.125	4 mm	7x30 mm	125 mm	24,5 mm	95 mm	220 mm	60 g
B198.045.125	4,5 mm	7x30 mm	125 mm	24,5 mm	95 mm	220 mm	69 g
B198.050.150	5 mm	8x30 mm	150 mm	30 mm	105 mm	255 mm	74 g
B198.055.150	5,5 mm	8x30 mm	150 mm	30 mm	105 mm	255 mm	74 g
B198.060.150	6 mm	9x30 mm	150 mm	30 mm	105 mm	255 mm	74 g
B198.060.150F	6 mm	11x27 mm	150 mm	34 mm	117 mm	255 mm	155 g
B198.070.150	7 mm	11x30 mm	150 mm	34 mm	117 mm	267 mm	105 g
B198.070.150F	7 mm	11x27 mm	150 mm	34 mm	117 mm	267 mm	155 g
B198.080.150	8 mm	12x30 mm	150 mm	34 mm	117 mm	267 mm	118 g
B198.080.150F	8 mm	12x27 mm	150 mm	34 mm	117 mm	267 mm	155 g
B198.090.150	9 mm	13x30 mm	150 mm	34 mm	117 mm	267 mm	110 g
B198.100.150	10 mm	14x30 mm	150 mm	34 mm	117 mm	267 mm	164 g
B198.110.150	11 mm	16x30 mm	150 mm	34 mm	117 mm	267 mm	170 g
B198.120.150	12 mm	17x30 mm	150 mm	34 mm	117 mm	267 mm	170 g
B198.130.150	13 mm	18x30 mm	150 mm	34 mm	117 mm	267 mm	170 g
B198.140.150	14 mm	19x30 mm	150 mm	34 mm	117 mm	267 mm	185 g
SB198.040.125	4 mm	7x30 mm	125 mm	24,5 mm	95 mm	220 mm	64 g
SB198.045.125	4,5 mm	7x30 mm	125 mm	24,5 mm	95 mm	220 mm	73 g
SB198.050.150	5 mm	8x30 mm	150 mm	30 mm	105 mm	255 mm	78 g
SB198.055.150	5,5 mm	8x30 mm	150 mm	30 mm	105 mm	255 mm	78 g
SB198.060.150	6 mm	9x30 mm	150 mm	30 mm	105 mm	255 mm	78 g
SB198.060.150F	6 mm	11x27 mm	150 mm	34 mm	117 mm	255 mm	159 g
SB198.070.150	7 mm	11x30 mm	150 mm	34 mm	117 mm	267 mm	109 g
SB198.070.150F	7 mm	11x27 mm	150 mm	34 mm	117 mm	267 mm	159 g
SB198.080.150	8 mm	12x30 mm	150 mm	34 mm	117 mm	267 mm	122 g
SB198.080.150F	8 mm	12x27 mm	150 mm	34 mm	117 mm	267 mm	159 g
SB198.090.150	9 mm	13x30 mm	150 mm	34 mm	117 mm	267 mm	114 g
SB198.100.150	10 mm	14x30 mm	150 mm	34 mm	117 mm	267 mm	168 g
SB198.110.150	11 mm	16x30 mm	150 mm	34 mm	117 mm	267 mm	174 g
SB198.120.150	12 mm	17x30 mm	150 mm	34 mm	117 mm	267 mm	174 g
SB198.130.150	13 mm	18x30 mm	150 mm	34 mm	117 mm	267 mm	174 g
SB198.140.150	14 mm	19x30 mm	150 mm	34 mm	117 mm	267 mm	189 g

Follow the Fish!

