

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1726722004](#)
Status: **Active**
Overview:
Description: 7.50mm Pitch Super Sabre Receptacle Crimp Housing, UL 94V-0, 4 Circuits

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	Crimp Housings
Series	172672
Application	Power, Wire-to-Board, Wire-to-Wire
Overview	super_sabre
Product Name	Super Sabre
UPC	889056025713

Physical

Circuits (maximum)	4
Color - Resin	Black
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	3.399/g
Number of Rows	1
Packaging Type	Carton
Panel Mount	No
Pitch - Mating Interface	7.50mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +125°C

Electrical

Current - Maximum per Contact	34.0A
-------------------------------	-------

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-44441-001-001
Product Specification	PS-171825-001-001
Sales Drawing	1726720000-SD-000
Test Summary	TS-171825-001-001

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[172672](#) Series

Mates With

Super Sabre Vertical Header [172042](#) .
Super Sabre Right Angle Header [172043](#) .
Super Sabre Plug Housing [172673](#) , [43680](#)

Use With

[171825](#) Super Sabre Female Crimp
Terminal